


Capsules

Specifications

Order code	Description	Watts (energy used)	Base type	Lumens (light output)	Life (hours)	Colour temp (°k)	CRI	MOL (mm)	Max diameter (mm)	Weight (g)
HALOGEN SAVER CAPSULE G9										
HS18G9 230/240V	18W HALOGEN SAVER CAPSULE G9 230V/240V	18	G9	210	2000	2800K	100	43	13	31.
HS28G9 230V/240V	28W HALOGEN SAVER CAPSULE G9 230V/240V	28	G9	370	2000	2800K	100	43	13	3.1
HS42G9 230V/240V	42W HALOGEN SAVER CAPSULE G9 230V/240V	42	G9	630	2000	2800K	100	43	13	3.1
HS53G9 230V/240V	53W HALOGEN SAVER CAPSULE G9 230V/240V	53	G9	835	2000	2800K	100	43	13	3.35
HS70G9 230V/240V	70W HALOGEN SAVER CAPSULE G9 230V/240V	70	G9	1180	2000	2800K	100	43	13	3.35
HALOGEN CAPSULE JC G4										
HJC10G4 12V	10W HALOGEN CAPSULE JC G4 12V	10	G4	120	2000	2800K	100	30	8	1.1
HJC20G4 12V	20W HALOGEN CAPSULE JC G4 12V	20	G4	300	2000	2800K	100	30	8	1.1
HALOGEN CAPSULE JC G6.35										
HJC20G6.35 12V	20W HALOGEN CAPSULE JC G6.35 12V	20	G6.35	300	2000	2800K	100	30	8	1.9
HJC35G6.35 12V	35W HALOGEN CAPSULE JC G6.35 12V	35	G6.35	550	2000	2800K	100	37	10	1.9
HJC50G6.35 12V	50W HALOGEN CAPSULE JC G6.35 12V	50	G6.35	855	2000	2800K	100	37	10	1.9



CAPSULE